




AVANT AIR+
Screening Audiometer

Ideal Audiometer for Traveling

Use for Community Screenings where
Only Air Thresholds Are Needed.

MedRx[®]

888-392-1234

To Schedule An Online Demo



AVANT AIR+

Technical Specs

Standards: Screening Audiometer As Per ANSI S3.6, IEC 60645-1, Type 4; Tone Audiometry

Outputs: DD65v2 Headphones

Frequency Range: Air: 125 Hz – 8 kHz

Max Output: Air Conduction: 100 dB HL For Mid-Range Frequencies

Attenuation: 1 dB Step Or 5 dB Step, User Selectable

Compatible with: Noah, TIMS®, Blueprint OMS And Sycle

Power Requirements: USB-Powered

Dimensions: Approx. 12 cm x 12 cm x 3 cm (L x W x H)
Approx. 5" x 5" x 1" (L x W x H)

Weight: < 500 g < 1 lb

Standard Accessories: DD65v2 Headphones, Patient Response Switch, Talkback Microphone, Operator Mic / Monitor Headset, Software & Manuals, Carrying Case

Optional Accessories: DD450 Headphones, DD45 Headphones Or Insert Earphones

MedRx Minimum Computer Specs:

Windows® PC compatible computer, Intel™ i5, 2.0 GHz or better. 4 GB RAM. 20 GB free hard drive space. Available 2.0 USB Port. Windows 10 or 11 Professional, Compatible with 3.0 USB.

AVANT AIR+ Features

- Air Threshold Testing
- Automatic Air Audiometry Testing
- 125 Hz - 8 kHz
- Small Footprint: Approx. 5" x 5" x 1" (L x W x H)
Approx. 12 cm x 12 cm x 3 cm (L x W x H)
- PC-based via USB Connection
- HID device - True Plug and Play
- Noah, TIMS, Blueprint OMS and Sycle Compatible



Good Things Come In Small Packages

MedRx, Inc

1200 Starkey Rd. #105

Largo, FL 33771 U.S.A.

888-392-1234 • 727-584-9600

Fax: 727-584-9602

Email: sales@medrx-diagnostics.com

www.medrx-diagnostics.com



AVANT AIR+ comes standard with the DD65v2 Headphones.

MX-AIR-DS-1 Rev. 4

